



## BENEFITS

- Consistent cell size and structure
- Outstanding purity
- Exceptional isotropic physical performance
- Extremely low odour

## SIREX EVA N35

SIREX® EVA N35 is a closed cell, high-performance crosslinked PE foam. SIREX® EVA N35 has a very fine and uniform cell structure. SIREX® EVA N35 is chemically inert, odourless, environmentally friendly, recyclable and free from harmful chemical additives. SIREX® EVA N35 is delivered in blocks and is on demand also available in sheets at desired thickness, strips, with self-adhesive and much more. Don't hesitate to contact us for additional information regarding the possibilities.



ISMT B.V.  
Küppersweg 18  
NL - 2031 EC Haarlem



Niederlassung Deutschland  
Flughafenstraße 59  
D - 70629 Stuttgart



+31 (0)88 018 4900  
+49 (0)7154 3091



[www.ismt-bv.com](http://www.ismt-bv.com)  
[sales@ismt-bv.com](mailto:sales@ismt-bv.com)



Our documentation, product information, recommendations and price lists have been compiled to the best of our knowledge and ability, and are based on average values and data known at the time of writing. They are not legally binding in any way

**TECHNICAL INFORMATION**

PROPERTY	TEST STANDARD	UNITS	TYPICAL VALUE
<b>Apparent Density</b> Skin/Skin	BS EN ISO 7214:2012	kg/m <sup>3</sup>	35 (nominal)
<b>Cell Size (Cell Diameter)</b>	Internal	mm	0.5
<b>Compression Stress-Strain</b> 25% compression 50% compression	BS EN ISO 7214:2012 25 mm cell-cell	kPa	52 118
<b>Tensile Strength</b>	BS EN ISO 7214:2012	kPa	545
<b>Tensile Elongation</b>		%	145
<b>Compression Set</b> 25% comp., 22hr, 23°C ½ h recovery 24 h recovery	BS EN ISO 7214:2012 25 mm cell-cell	% set	10 3
<b>Tear Strength</b>	BS EN ISO 8067:2008 Method B	N/m	1970
<b>Shore Hardness</b> OO Scale	BS EN ISO 868:2003		50
<b>Recommended maximum operating temperature*</b>	Internal	°C	70
<b>Water Absorption</b>	ISO 2896:2001 Ed3.	%	<1

**\* RECOMMENDED MAXIMUM OPERATING TEMPERATURE**

The maximum operating temperature shown is defined as the temperature which will typically cause a linear shrinkage of 5% after a 24hr exposure period, using sample dimensions of 100mm x 100mm x 25mm. This figure is provided for general guidance only. The actual level of shrinkage the foam will undergo at any particular temperature is dependant on a number of system variables such as, sample dimensions, cell size, loading conditions and exposure period.