



BENEFITS

- Consistent cell size and structure
- Outstanding purity
- Exceptional isotropic physical performance
- Extremely low odour

SIREX EVA N50

SIREX® EVA N50 is a closed cell, high-performance crosslinked PE foam. SIREX® EVA N50 has a very fine and uniform cell structure. SIREX® EVA N50 is chemically inert, odourless, environmentally friendly, recyclable and free from harmful chemical additives. SIREX® EVA N50 is delivered in blocks and is on demand also available in sheets at desired thickness, strips, with self-adhesive and much more. Don't hesitate to contact us for additional information regarding the possibilities.



ISMT B.V.
Küppersweg 18
NL - 2031 EC Haarlem



Niederlassung Deutschland
Flughafenstraße 59
D - 70629 Stuttgart



+31 (0)88 018 4900
+49 (0)7154 3091



www.ismt-bv.com
sales@ismt-bv.com



Our documentation, product information, recommendations and price lists have been compiled to the best of our knowledge and ability, and are based on average values and data known at the time of writing. They are not legally binding in any way



DATASHEET
SIREX® EVA N50

TECHNICAL INFORMATION

PROPERTY	TEST STANDARD	UNITS	TYPICAL VALUE
Apparent Density Skin/Skin	BS EN ISO 7214:2012	kg/m ³	50 (nominal)
Cell Size (Cell Diameter)	Internal	mm	0.4
Compression Stress-Strain 25% compression 50% compression	BS EN ISO 7214:2012 25 mm cell-cell	kPa	50 116
Tensile Strength	BS EN ISO 7214:2012	kPa	749
Tensile Elongation		%	243
Compression Set 25% comp., 22hr, 23°C ½ h recovery 24 h recovery	BS EN ISO 7214:2012 25 mm cell-cell	% set	9 2
Tear Strength	BS EN ISO 8067:2008 Method B	N/m	2880
Shore Hardness OO Scale	BS EN ISO 868:2003		46
Recommended maximum operating temperature*	Internal	°C	65
Water Absorption	ISO 2896:2001 Ed3.	%	<1

*** RECOMMENDED MAXIMUM OPERATING TEMPERATURE**

The maximum operating temperature shown is defined as the temperature which will typically cause a linear shrinkage of 5% after a 24hr exposure period, using sample dimensions of 100mm x 100mm x 25mm. This figure is provided for general guidance only. The actual level of shrinkage the foam will undergo at any particular temperature is dependant on a number of system variables such as, sample dimensions, cell size, loading conditions and exposure period.



Our documentation, product information, recommendations and price lists have been compiled to the best of our knowledge and ability, and are based on average values and data known at the time of writing. They are not legally binding in any way

